Face Velocity		300	400	500	600	
1 // 1/ / / / / / / / / / / / / / / / /	CFM	524	698	873	1048	1222
	Static Pressure (in W.C.)					-0.128
	Total Pressure (in W.C.)	-0.018	-0.032	-0.050	-0.072	-0.098
Note: Tested without filters. Typical capacity is 2 CFM per square inch of nominal filter						
area. Recommended face velocity is 300-450 FPM. Velocities higher will decrease filter						
performance, increase flow resistance, and possibly be of noise concern. Velocity						
measured 1" from face.						